

# CM2600 Chamber

- 26 Tire Chamber, 480 volt, 3 phase, 250 amps, adjustable if there is not enough amperage
- Push Button Hydraulic – Electric Door Open / Close
- Omron PLC – PLC controls the entire cycle, so if all the set points are not correct, the cure cycle will not begin
- Data logging of complete cycle and alarms
- 15" Touch Screen Control, diagnostic view
- Chamber wall temperature display
- Thermocouple plug-in for independent check
- 1 Stainless Steel Manifold (envelope control pressure)
- Oil Filled Air Gauges
- 24 heating elements
- 20 HP fan motor
- Hoses, Long, 26 Inlets
- 1 Lift Out Bridge (monorail)
- 2 Upright Legs

## OPTION

EMS – Envelope Monitoring System – each line is separately checked during cure cycle.

SCR controller for heating elements can be connected to internet for trouble shooting.

